

# MFU filtered air exhaust connection on the outside



📌 Sectors

📌 Applications **Mobile**

📌 Issues **Fumes**

COD: KITSCARICESTMFU

Lateral connection diam. 200 mm for hose to discharge filtered air outside from MFU purifiers all.

## Insight

With this hose connection, filtered air from MFU purifiers can be expelled into a flexible hose (to be purchased separately) so that it cannot be fed back into the room.


### Kit contents:

- side panel for hose connection diam. 200

Optional/not included:

- flexible hose made of sturdy PVC reinforced with harmonic steel spiral diam. 200mm





**Kit contents:**

- side panel for connecting flexible hose, diameter 200

**On request / not included:**

- flexible hose in sturdy PVC reinforced with harmonic steel spiral, diameter 200 mm, 10 m lengths.



## Dimensions

Code	Ø mm
KITSCARICESTMFU	200

## Technical Data

Code	Pipe diameter mm	Attachment
KITSCARICESTMFU	200	200 mm diameter



## Related Products



### MFUHCO fume extractor

MFU21HCO0000000


MFUHCO high-performance mobile fume and exhaust extractor on wheels for professional use, with suction arm, HEPA H13 99.99% absolute filtration, and activated carbon filters.



### MFU-HW welding fume extractor with superflex arm

MFU21HWXF000000

High-performance mobile welding fume extractor for professional use, with HEPA H13 99.99% absolute filtration



### MFU-HW welding fume extractor with red arm

MFU21HWR0000000

MFU-HW mobile extractor for welding fumes and micro-dust with red arm, high performance for professional use, with HEPA H13 99.99% absolute filtration



### MFU-HWF23 welding fume extractor double arm 3m

MFU21HW32F00000

MFU-HWF23 mobile welding fume extractor with double superflex arm, with H13 99.99% efficiency filtration.

