

Filtered air outlet connection MFU

📌 Sectors

📌 Applications: **Mobile**

📌 Issues **Fumes**

COD: KITSCARICESTMFU



Lateral connection diam. 200 mm for hose to discharge filtered air outside from MFU purifiers all.

Detailed description

With this hose connection, filtered air from MFU purifiers can be expelled into a flexible hose (to be purchased separately) so that it cannot be fed back into the room.


Kit contents:

- side panel for hose connection diam. 200

Optional/not included:

- flexible hose made of sturdy PVC reinforced with harmonic steel spiral diam. 200mm



**Kit contents:**

- side panel for hose connection diam. 200

On request / not included

- flexible hose made of sturdy reinforced PVC with harmonic steel spiral diameter 200 mm, 10 m pieces



Dimensions

| Code | Ø mm |
|-----------------|---------|
| KITSCARICESTMFU | 200 |

Technical Data

| Code | Pipe diameter mm | Attachment |
|-----------------|---------------------|-----------------|
| KITSCARICESTMFU | 200 | 200 mm diameter |



Related products



MFU-HCO fumes extractor

MFU21HCO0000000


MFUHCO high-performance mobile wheeled fume and exhalation extractor for professional use, with 2mt suction arm, HEPA H13 99.99% absolute filtration and activated carbon



MFU-HW welding fume extractor with superflex arm

MFU21HWXF000000

Mobile extractors for welding fumes and micro-dust, high performance for professional use, with HEPA H13 99.99% absolute filtration



MFU-HW welding fume extractor with red arm

MFU21HWR0000000

Mobile extractors for welding fumes and micro-dust, high performance for professional use, with HEPA H13 99.99% absolute filtration



MFU-HWF23 welding fume extractor double arm 3m

MFU21HW32F00000

Mobile welding fume extractor with superflex double arm, with filtration efficiency H13 99.99%.

